

Henry 2DW1 LWD RT 200TVD


IDEAL Version: ID13_OC_11 <TVD> Vertical Scale: 1:200


Graphics File Created: 16-Sep-2008 13:44

PIP SUMMARY

- └ ARC Gamma Ray Samples
- └ IMP RP28 PIP

		ARC BHCorr Phase-Shift Resistivity 40-in. at 2 MHz, Real-Time (P40H_RT)	
		0.2	200
		(OHMM)	
ARC Gamma Ray, Real-Time (ARC_GR_RT) (GAPI)	0	ARC BHCorr Phase-Shift Resistivity 28-in. at 2 MHz, Real-Time (P28H_RT)	
	200	(OHMM)	
		0.2	200
ROP*5 (ROP5) (M/HR)	0	ARC BHCorr Attenuation Resistivity 40-in. at 2 MHz, Real-Time (A40H_RT)	
	200	(OHMM)	
		0.2	200
MWD Collar RPM (CRPM_RT) (RPM)		PKPK RPM (Stick RT) (RPM)	
		0	250
		0	500





ROP*5 (ROP5) 200 (M/HR) 0	PKPK RPM (Stick_RT) (RPM)	ARC BHCorr Attenuation Resistivity 40-in. at 2 MHz, Real-Time (A40H_RT)	
	0 500	0.2	(OHMM) 200
ARC Gamma Ray, Real-Time (ARC_GR_RT) 0 (GAPI) 200	MWD Collar RPM (CRPM_RT) (RPM)	ARC BHCorr Phase-Shift Resistivity 28-in. at 2 MHz, Real-Time (P28H_RT)	
	0 250	0.2	(OHMM) 200
		ARC BHCorr Phase-Shift Resistivity 40-in. at 2 MHz, Real-Time (P40H_RT)	
		0.2	(OHMM) 200
PIP SUMMARY			
└ ARC Gamma Ray Samples			
└ IMP RP28 PIP			