

Henry2DW1ST1 LWD RT 200TVD


IDEAL Version: ID13_OC_11 <TVD> Vertical Scale: 1:200


Graphics File Created: 07-Oct-2008 03:04


PIP SUMMARY


- ARC Gamma Ray Samples
- ARC Resistivity Samples
- IMP RP28 PIP


		ARC BHCorr Attenuation Resistivity 40-in. at 400 KHz, Real-Time (A40L_RT)	
		0.2	200
		(OHMM)	
		ARC BHCorr Phase-Shift Resistivity 40-in. at 2 MHz, Real-Time (P40H_RT)	
		0.2	200
		(OHMM)	
		ARC BHCorr Phase-Shift Resistivity 16-in. at 2 MHz, Real-Time (P16H_RT)	
		0.2	200
		(OHMM)	
ARC Gamma Ray, Real-Time (ARC_GR_RT) (GAPI)	0	ARC BHCorr Phase-Shift Resistivity 28-in. at 2 MHz, Real-Time (P28H_RT)	
	200	0.2	200
		(OHMM)	
		MWD Collar RPM (CRPM_RT) (RPM)	
		0	200
		ROP*5 (ROP5) (M/HR)	
		0	200
		PKPK_RPM (Stick_RT) (RPM)	
		0	400
		ARC BHCorr Attenuation Resistivity 40-in. at 2 MHz, Real-Time (A40H_RT)	
		0.2	200
		(OHMM)	









































ROP*5 (ROP5) (M/HR)	0200	PKPK RPM (Stick_RT) (RPM)	0400	ARC BHCorr Attenuation Resistivity 40-in. at 2 MHz, Real-Time (A40H_RT)	
				0.2	200
ARC Gamma Ray, Real-Time (ARC_GR_RT) (GAPI)	0200	MWD Collar RPM (CRPM_RT) (RPM)	0200	ARC BHCorr Phase-Shift Resistivity 28-in. at 2 MHz, Real-Time (P28H_RT)	
				0.2	200
				ARC BHCorr Phase-Shift Resistivity 16-in. at 2 MHz, Real-Time (P16H_RT)	
				0.2	200
				ARC BHCorr Phase-Shift Resistivity 40-in. at 2 MHz, Real-Time (P40H_RT)	
				ARC BHCorr Attenuation Resistivity 40-in. at 400 KHz, Real-Time (A40L_RT)	
				0.2	200

PIP SUMMARY

└ ARC Gamma Ray Samples

- ARC Gamma Ray Samples
- ARC Resistivity Samples
- IMP RP28 PIP